

RhinoBlock_{TM}

PRODUCT DATA SHEET

RB201™ Permanent Blockout

Description:

Color: BlueSolids: 19%

Viscosity: 4,500 / 5,500 cPs at 20 RMP-26C

RhinoBlock 201TM is a two-part blockout that is easily spread onto a screen. RB201TM is recommended for use with Plastisol, UV and Solvent inks.

RB202™ Water Soluble Blockout / Thin

Description:

Color: RedSolids: 18%

• Viscosity: 4,500 / 5,500 cPs at 20 RMP-26C

RhinoBlock 202TM is an easy to spread screen blockout. RB202TM is recommended for use with Plastisol, UV and Solvent inks. RB202TM dissolves in water and can be easily reclaimed.

RB203™ Water Soluble Blockout / Thick

Description:

Color: RedSolids: 18%

• Viscosity: 9,500 / 10,500 cPs at 20 RMP-26C

RhinoBlock 203TM is a fast drying screen blockout. RB203TM is recommended for use with Plastisol, UV and Solvent inks. RB203TM dissolves in water and can be easily reclaimed. This product can also be thinned with water.

It is the responsibility of the screen printer to test RhinoBlock; review the MSDS prior to use to evaluate whether or not the product is correct for the application intended.



RhinoBlock PRODUCT DATA SHEET

Once you have created a stencil using Capillary Film or Emulsion, you are ready to block out the rest of the screen. The stencil should be dry.

Next, place the frame squeegee side down on a work table. With your blockout in a squeeze bottle, apply a small amount on the open area of mesh that you want to blockout.

Using a plastic spreader, move the blockout around the area up to the stencil and apply a thin layer. Once dry, this will keep the ink from penetrating the mesh. (It might be necessary to spread the blockout on the squeegee side of the screen if too much is pushed thru the mesh).

Keep in mind that blockout does not harden like emulsion, so it will wash out with water if you are not using a permanent blockout like RB201. When using RB201, add the catalyst first if you want it to be a solvent resistant blockout.